

Varistar CP Steel Door, Perforated With Multi-Point Locking

Power Utilities

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

VLASTNOSTI

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Výška	Šířka	Barva	Kód barvy	Locking Type
21630-533	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-534	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-535	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-536	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-537	33 U	1600 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-538	33 U	1600 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-539	38 U	1800 mm	600 mm	Black Grey	RAL 7021	4-Point Locking

Katalogové číslo	Rack Height	Výška	Šířka	Barva	Kód barvy	Locking Type
21630-540	38 U	1800 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-541	42 U	2000 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-542	42 U	2000 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-543	47 U	2200 mm	600 mm	Black Grey	RAL 7021	5-Point Locking
21630-544	47 U	2200 mm	800 mm	Black Grey	RAL 7021	5-Point Locking

Table 2/2

Katalogové číslo	Materiál	Product Type	Typ
21630-533	Ocel	Cabinet Door	Steel Door, Perforated
21630-534	Ocel	Cabinet Door	Steel Door, Perforated
21630-535	Ocel	Cabinet Door	Steel Door, Perforated
21630-536	Ocel	Cabinet Door	Steel Door, Perforated
21630-537	Ocel	Cabinet Door	Steel Door, Perforated
21630-538	Ocel	Cabinet Door	Steel Door, Perforated
21630-539	Ocel	Cabinet Door	Steel Door, Perforated
21630-540	Ocel	Cabinet Door	Steel Door, Perforated
21630-541	Ocel	Cabinet Door	Steel Door, Perforated
21630-542	Ocel	Cabinet Door	Steel Door, Perforated
21630-543	Ocel	Cabinet Door	Steel Door, Perforated
21630-544	Ocel	Cabinet Door	Steel Door, Perforated

DALŠÍ PODROBNOSTI O PRODUKTU

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte