

Varistar CP Swing Frame for 600 mm Width

Power Utilities

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° movement and flexible pivot point.

VLASTNOSTI

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" sub racks (maximum depth 200 mm)

120° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Barva	Kód barvy	Výška	Materiál	Product Type
21630-668	24 U	Black Grey	RAL 7021	1200 mm	Ocel	Cabinet/Rack Frame
21630-670	29 U	Black Grey	RAL 7021	1400 mm	Ocel	Cabinet/Rack Frame
21630-672	33 U	Black Grey	RAL 7021	1600 mm	Ocel	Cabinet/Rack Frame
21630-674	38 U	Black Grey	RAL 7021	1800 mm	Ocel	Cabinet/Rack Frame
21630-676	42 U	Black Grey	RAL 7021	2000 mm	Ocel	Cabinet/Rack Frame
21630-678	47 U	Black Grey	RAL 7021	2200 mm	Ocel	Cabinet/Rack Frame

Table 2/2

Katalogové číslo	Stupeň krytí	Šířka
21630-668	IP20	600 mm
21630-670	IP20	600 mm
21630-672	IP20	600 mm
21630-674	IP20	600 mm
21630-676	IP20	600 mm
21630-678	IP20	600 mm

DALŠÍ PODROBNOSTI O PRODUKTU

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE