

19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



VLASTNOSTI

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFIKACE

Product Type: Assembly Kit

Povrchová úprava: Pozinkovaná Ocel

Table 1/2

Katalogové číslo	Length	Množství v balení	Thread Size	Materiál	Produktová řada	Typ
------------------	--------	-------------------	-------------	----------	-----------------	-----

21190-095		4	M6	Ocel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit
21120-196	16mm	4	M6	Ocel		Mounting Kit, Grounding
21100-435		8	M6	Ocel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-215		32	M6	Ocel		Mounting Kit
21101-809		50	M6	Ocel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-214		50	M6	Ocel		Mounting Kit
21120-198	16mm	50	M6	Ocel		Mounting Kit, Grounding

21101-810		100	M6	Ocel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-216		100	M6	Ocel		Mounting Kit
21120-213		4	M6	Ocel		Mounting Kit
21120-199	13mm	100	M6	Ocel		Mounting Kit, Grounding
21120-197	16mm	32	M6	Ocel		Mounting Kit, Grounding
21190-435		32	M6	Ocel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit

Table 2/2

Katalogové číslo	Works With	Certifications	Rychlé odeslání
21190-095	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	Ne
21120-196	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne
21100-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	Ne
21120-215	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne

Katalogové číslo	Works With	Certifications	Rychlé odeslání
21101-809	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	Ne
21120-214	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne
21120-198	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne
21101-810	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	Ne
21120-216	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne
21120-213	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne
21120-199	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne
21120-197	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		Ne
21190-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE