

# 19" Cable Ducting

19" unit for easy and effective cable management (cable ducting).



## CERTIFICATIONS



## VLASTNOSTI

19" Front panel for cable ducting

## SPECIFIKACE

**Accessory Type:** Front panel  
**Product Type:** Front Panel  
**Materiál:** Ocel

Table 1/3

| Katalogové číslo | Rack Height | Mounting       | Množství v balení | Front Finish | Rear Finish | Kód barvy |
|------------------|-------------|----------------|-------------------|--------------|-------------|-----------|
| 20118-734        | 1U          | Screw-on Front | 1                 | Painted      | Painted     | RAL 7035  |
| 20118-767        | 1U          | Screw-on Front | 1                 | Painted      | Painted     | RAL 7021  |
| 20118-768        | 2U          | Screw-on Front | 1                 | Anodized     | Conductive  | RAL 7021  |

| Katalogové číslo | Rack Height | Mounting       | Množství v balení | Front Finish | Rear Finish | Kód barvy |
|------------------|-------------|----------------|-------------------|--------------|-------------|-----------|
| 20118-736        | 2U          | Screw-on Front | 1                 | Painted      | Painted     | RAL 7035  |

Table 2/3

| Katalogové číslo | Hloubka | EMC Shielding | Povrchová úprava          | Výška  | Rack Width | Typ             |
|------------------|---------|---------------|---------------------------|--------|------------|-----------------|
| 20118-734        | 1.5mm   | No            | Strukturovaný<br>Práškový | 43.6mm | 95HP       | 19" Front Panel |
| 20118-767        | 1.5mm   | No            | Strukturovaný<br>Práškový | 43.6mm | 95HP       | 19" Front Panel |
| 20118-768        | 1.5mm   | No            | Strukturovaný<br>Práškový | 88.1mm | 95HP       | 19" Front Panel |
| 20118-736        | 1.5mm   | No            | Strukturovaný<br>Práškový | 88.1mm | 95HP       | 19" Front Panel |

Table 3/3

| Katalogové číslo | Šířka | Rychlé odeslání |
|------------------|-------|-----------------|
| 20118-734        | 483mm | Ne              |
| 20118-767        | 483mm | Ne              |
| 20118-768        | 483mm | Ne              |
| 20118-736        | 483mm | Ne              |

## DALŠÍ PODROBNOSTI O PRODUKTU

Please order 19" assembly kit separately.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**