


ATCA Front Panel, Al-Profile, Reinforced With Spring Loading



AdvancedTCA front panel for spring-loaded IEA handle with die-cast end piece.

CERTIFICATIONS



VLASTNOSTI

Configuration: Front panel with IEA handle (with/without spring loading)

Al extrusion; for mesh EMC sealing

SPECIFIKACE

Hloubka (D):	1mm
Rack Width:	6HP
Rack Height:	8U
Materiál:	Hliník
Accessory Type:	Front panel
Product Type:	Front Panel


Table 1/2

Katalogové číslo	Množství v balení	Typ rukojeti	Front Finish	Rear Finish	Povrchová úprava	Výška (H)
31596-900	1	Lever	Raw	Raw	Passivated	323.15mm
31596-899	1	Plunger	Raw	Raw	Passivated	323.15mm

Table 2/2

Katalogové číslo	Šířka (W)	Rychlé odeslání
31596-900	29mm	Ne
31596-899	29mm	Ne

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE