

CPCI Serial System With Pluggable PSU, 4 U, 9 Slot

4 U CompactPCI Serial System with vertical Card Cage for nine 3 U Boards and one 3U Pluggable Power Supply.



CERTIFICATIONS



VLASTNOSTI

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG CPCI-S.0

System with vertical card cage. For Board format 3U

Backplane 9 slot, 3U CompactPCI Serial (single star Ethernet topology), System slot left

Heat dissipation via 1 U hot-swap fan unit

Supports PCIe up to Gen3, USB 2.0 and 3.0, SATA up to Rev 3.0, and Ethernet up to 10 GBase-T

Retrofittable air filter

SPECIFIKACE

Table 1/3

Katalogové číslo	Product Type	Number of Slots	Typ	Backplane Type	Data Transfer	Power per Slot
24579-421	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

Katalogové číslo	Product Type	Number of Slots	Typ	Backplane Type	Data Transfer	Power per Slot
24579-416	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

Table 2/3

Katalogové číslo	Vstupní napětí AC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
24579-421	100 – 240V	Bottom to Top	4U	(2) Pluggable PSU	Yes	Yes
24579-416	100 – 240V	Bottom to Top	4U	(1) Pluggable PSU	Yes	No

Table 3/3

Katalogové číslo	Complies With	Hloubka	Výška	Množství v balení	Rychlé odeslání
24579-421	PICMG CPCI-S.0 R2.0	275mm	177mm	1	Ne
24579-416	PICMG CPCI-S.0 R2.0	275mm	177mm	1	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Preference types can be ordered directly from stock, other configurations on request.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE