


Comptec Folding Handle, RAL 7016, Die-Cast

KATALOGOVÉ ČÍSLO

20225-439



Folding handles can be used instead of the pre-mounted handles shells.

CERTIFICATIONS



VLASTNOSTI

Load-carrying capacity: 50 kg/pair

Lock-in in folded and unfolded position

For case protection class up to IP 40

VLASTNOSTI PRODUKTU

Product Type: Handle

Typ: Static

Works With: Cases

Typ rukojeti: Folding Handle

Materiál: Hliník

Barva: Dark Grey

Static Load: 50kg

Množství v balení: 2

Povrchová úprava: Strukturovaný Práškový

Net Weight: 0.575kg

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE