

AC Fan, 230 VAC, 119 x 119 x 25 mm, 84 m³h

KATALOGOVÉ ČÍSLO

20713-142

Axial fan, 119 mm, with AC input. Replacement part for 1 U fan trays.



CERTIFICATIONS



VLASTNOSTI

119 mm DC fan with plug for connection cable

VLASTNOSTI PRODUKTU

Product Type: Fan

Works With: 19" Fan Trays

Šířka: 119mm

Length: 119mm

Výška: 25mm

Napětí střídavé: 230V

Frequency: 50/60 Hz

Airflow @ 50 Hz: 84m³/h

Airflow @ 60 Hz: 90m³/h

Noise Level @ 50 Hz: 29dB(A)

Noise Level @ 60 Hz: 30dB(A)

Power @ 50 Hz: 8W

Power @ 60 Hz: 7W

Max Static Pressure: 23Pa

Okolní teplota: 70°C

Gross Weight: 0.347kg

Množství v balení: 1

DALŠÍ PODROBNOSTI O PRODUKTU

Please order connection cable and protective grille separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE