


Plug-In Unit Kit for FMC With IEL Handle black, U-shaped Front Panel Shielded (Textile), 3 U, 4 HP

KATALOGOVÉ ČÍSLO

20836-253



The FMC bezel are in accordance with Vita 57.1 specification. Covers the cut out in the overall front panel.

CERTIFICATIONS



VLASTNOSTI

In accordance with Vita 57.1 specification

For single 69.0 x 76.5 mm or double 139.0 x 76.5 mm modules

AI-Profile plug-in unit with IEL handle

VLASTNOSTI PRODUKTU

Rack Height: 3U

Množství v balení: 1

Typ rukojeti: IEL

Mounting: Screw-on Front

EMC Gasket Type: Textile

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: No

Complies With: FMC Mezzanine, Vita 57.1

EMC Shielding: Yes

Povrchová úprava: Anodized; Passivated

Výška: 128.4mm

Materiál: Hliník

Product Type: Front Panel

Rack Width: 4HP

Typ: Front Panel with Handle (PIU)

Šířka: 20mm

Net Weight: 0.1kg

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE