

Varistar CP Shortened Rear Panel with Recessed Mounting Plate, EMC, glazed steel, 2200H 800W

KATALOGOVÉ ČÍSLO

21630-914



Recessed connection plates are needed for connectors which don't protrude out of the plane of the cabinet

VLASTNOSTI

Intelligent cable management design with recessed connection plates

Connection plate is 400 mm high

For recessed plate: Plate recessed by 40 mm

VLASTNOSTI PRODUKTU

Rack Height: 47U

Výška: 2200mm

Šířka: 800mm

Množství v balení: 1

Povrchová úprava: Strukturovaný Práškový

Materiál: Ocel; Stainless Ocel

Produktová řada: Varistar CP

Product Type: Cabinet/Rack Panel

Stupeň krytí: IP55

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE