

240 Card-Lok

KATALOGOVÉ ČÍSLO

240-4.80H



The Series 240 features a higher weight, narrow profile ideal for densely populated enclosures.

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

CERTIFICATIONS



VLASTNOSTI

Length 97 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

For cold wall applications

Profile 6.10 mm (0.240") x 4.57 mm (0.180")

3 segment, non-shafted design

Weight 0.86 g/cm (0.077 oz/')

Flexible mounting options

Min expansion 5.59 mm (0.220")

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

DSCC 84103 / DSCC CID 59590

Screw actuated

Average clamp force (4.80", black anodized) = 314 lbs

VLASTNOSTI PRODUKTU

Product Type: PCB Retainer

Materiál: Hliník

Typ: Non-shafted

Thermal Performance: Average

Profile: 6.10 x 4.57 mm

Clamp Force: 136 – 181kgf

Gap Width: PCB + (5.0 - 5.9 mm)

DALŠÍ PODROBNOSTI O PRODUKTU

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE