


# PCB Solder Side Cover, CPCI, 3 U, 100 mm x 160 mm,

## KATALOGOVÉ ČÍSLO

**24579-037**



A solder side cover protects the solder side of a PCB mechanically.

## CERTIFICATIONS



## VLASTNOSTI

Cover is perforated for better cooling of components

Mechanical protection of solder side

## VLASTNOSTI PRODUKTU

Rack Height: 3U

Množství v balení: 1

Hloubka (D): 160mm

Materiál: Plast

Product Type: Cover

Typ: Solder Side Cover

Šířka (W): 100mm


Works With: Front Panels

Net Weight: 0.013kg

## DALŠÍ PODROBNOSTI O PRODUKTU

Fixing clips are required for mounting the perforated covers; please order separately.

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**