

CPCI Serial R3.0 System With Pluggable PSU, 4 U, 9 Slot, With Rear I/O

KATALOGOVÉ ČÍSLO

24579-451



4 U CompactPCI Serial R3.0 System, with vertical Card Cage for nine 3 U Boards and one 3U Pluggable Power Supply.

VLASTNOSTI

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG CPCI-S.0 R3.0

Supports PCIe Gen 4, 10 Gbase-T, S-ATA 3 and USB 3.2 Gen 2

Ethernet interface is 10GBASE-KR and 10GBASE-T capable and 25GBASE-KR ready

System with vertical card cage. For Board format 3U

Backplane 9 slot, 3U CompactPCI Serial (single star Ethernet topology), System slot left

Heat dissipation via 1 U hot-swap fan unit

Retrofittable air filter

VLASTNOSTI PRODUKTU

Product Type: System

Number of Slots: 9

Typ: 19" Rack Mount

Backplane Type: 3 U CompactPCI Serial with Ethernet Star

Data Transfer: PCIe Gen4

Power per Slot: 40W

Vstupní napětí AC: 100 – 240V

Airflow Direction: Bottom to Top

Rack Height: 4U

Power Supply Type: (2) Pluggable PSU

Power Supply Included: Yes

Rear I/O: Yes

Complies With: PICMG CPCI-S.0 R3.0

Hloubka: 275mm

Výška: 177mm

Rack Width: 84HP

Slot Width: 4HP

System Slot: Left

DALŠÍ PODROBNOSTI O PRODUKTU

Preference types can be ordered directly from stock, other configurations on request.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE