



Horizontal Rail, Rear, Type H-ST, Heavy, Standard, 20 HP

KATALOGOVÉ ČÍSLO

34560-520



Combinations of horizontal rails and side panels

		$\Delta \sigma_{\perp}$ can be combined. $\Delta \sigma_{\parallel}$ combination: not recommended			
Pressure $\sigma_{\perp}$		-	+	+	Subst. OK (upper)
		+	Subst. OK (flexible)	Subst. OK (strong and Subst. OK (rigid) (stiffness)	+
Light $\sigma_{\parallel}$		Subst. OK (light)	Subst. OK (flexible)	+	+
		+	+	-	-
Thermal $\sigma_{\parallel}$		Subst. OK (light)	Subst. OK (flexible)	+	+
		+	+	-	-
Side stress		Subst. OK (light)	Subst. OK (flexible)	+	+
		+	+	-	-

The horizontal rail, type ST enables the isolated assembly of a backplane. The isolation is done by an insulation strip.

CERTIFICATIONS



VLASTNOSTI

For indirect backplane mounting with insulation strip

Standard where mechanical demands are high (H-ST)

Mounting top and bottom

< 28 HP not printed

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

VLASTNOSTI PRODUKTU

Rack Width: 20HP

Množství v balení: 1

Povrchová úprava: Anodized

Length: 106.68mm

Materiál: Hliník

Produktová řada: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Typ: Heavy, ST

Works With: Subracks; Cases

DALŠÍ PODROBNOSTI O PRODUKTU

Delivery is in standard pack multiples. Pricing is per individual item.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE