

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

KATALOGOVÉ ČÍSLO

34566-284



Combinations of horizontal rails and side panels

	Light	Front	Heavy	Rugged
Light	+	+	+	+
Front	+	+	+	+
Heavy	+	+	+	+
Rugged	+	+	+	+

Legend: "+" can be combined, "-" combination not recommended

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICATIONS



VLASTNOSTI

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

VLASTNOSTI PRODUKTU

Rack Width: 84HP

Množství v balení: 1

Povrchová úprava: Anodized

Length: 431.8mm

Materiál: Hliník

Produktová řada: EuropacPRO

Product Type: Horizontal Rail

Typ: Rugged, KD

Works With: Subracks

Gross Weight: 0.26kg

DALŠÍ PODROBNOSTI O PRODUKTU

Without M4 thread to front, without printing and without notch for 19" bracket.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE