


Horizontal Rail, Front, Type R-LD, Rugged, Long Lip , 84 HP

KATALOGOVÉ ČÍSLO

34566-384



Combinations of horizontal rails and side panels

 = can be combined,
  = combination not recommended

	Recessed A		Recessed B	Recessed C	Recessed D	Recessed E
Recessed A		-				
Recessed B			recessed B1 (fixed on the connector)	recessed B with pins and recessed B1 (fixed on the connector)	recessed B with pins and recessed B1 (fixed on the connector)	
Recessed C			recessed C1 (fixed)	recessed C with pins	-	-
Recessed D			-	-	-	-
Recessed E			-	-	-	-
Side panel						
	1000 x 1	Recessed A	Recessed B	Recessed C	Recessed D	Recessed E

 = can be combined,
  = combination not recommended

The rugged horizontal rail type can handle shock and vibration up to 25 g. It enables the use of IEEE handles.

CERTIFICATIONS



VLASTNOSTI

Type R-LD "rugged" horizontal rails with 3-hole fixing for increased robustness

For insertion/extraction of CompactPCI or, VME64x boards

With HP units printed from 28 HP upwards

Length 20, 28, 40, 42, 63, 84 HP or 1000 mm

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

VLASTNOSTI PRODUKTU

Rack Width: 84HP

Množství v balení: 1

Povrchová úprava: Anodized

Length: 431.8mm

Materiál: Hliník

Produktová řada: EuropacPRO

Product Type: Horizontal Rail

Typ: Rugged, LD

Works With: Subracks

Gross Weight: 0.259kg

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE