

266 Card-Lok

KATALOGOVÉ ČÍSLO

MVHA266-6.80TM2.5LK



The Series 266 features a ridged shafted design which provides more uniform clamping force over the length of the Card Lok, while maintaining wedge and body alignment for easier installation.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

VLASTNOSTI

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

Screw actuated

Weight 0.89 g/cm (0.080 oz/')

Flexible mounting options

3 segment, shafted design

Profile 5.72 mm (0.225") x 5.84 mm (0.230")

Length 96.5 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

Min expansion 7.37 mm (0.290")

Average clamp force (4.80", black anodized) = 238 lbs

For cold wall applications

VLASTNOSTI PRODUKTU

Product Type: PCB Retainer

Materiál: Hliník

Typ: Shafted

Thermal Performance: Average

Profile: 5.72 x 5.84 mm

Clamp Force: 91 – 136kgf

Gap Width: PCB + (6.0 - 6.9 mm)

DALŠÍ PODROBNOSTI O PRODUKTU

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE