

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Non-EMC shielded subrack for backplane mounting, light version.



CERTIFICATIONS



VLASTNOSTI

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPECIFIKACE

Materiál:	Hliník
Povrchová úprava:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Rukojeť v ceně
24564-131	3U	175mm	1	Backplane	160mm	No
24564-132	3U	235mm	1	Backplane	160mm, 220mm	No
24564-133	3U	295mm	1	Backplane	160mm, 220mm, 280mm	No
24564-431	6U	175mm	1	Backplane	160mm	No
24564-432	6U	235mm	1	Backplane	160mm, 220mm	No
24564-433	6U	295mm	1	Backplane	160mm, 220mm, 280mm	No

Table 2/2

Katalogové číslo	Mounting	Complies With	Rack Width	Static Load	Rychlé odeslání
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Ne
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Ne
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Ne
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Ne
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Ne
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE