

EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, Retrofit Shielding



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS



VLASTNOSTI

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

SPECIFIKACE

Materiál:	Hliník
Povrchová úprava:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Gasket Type
------------------	-------------	---------	-------------------	--------------	-------------	-------------

24553-132	3U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC
24553-133	3U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC
24553-134	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC
24553-432	6U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC
24553-433	6U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC
24553-434	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC

Table 2/2

Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	Rack Width	Static Load	Rychlé odeslání
24553-132	No	Rack	IEC 60297-3-103	84HP	11kg	Ne
24553-133	No	Rack	IEC 60297-3-103	84HP	11kg	Ne
24553-134	No	Rack	IEC 60297-3-103	84HP	11kg	Ne
24553-432	No	Rack	IEC 60297-3-103	84HP	11kg	Ne
24553-433	No	Rack	IEC 60297-3-103	84HP	11kg	Ne
24553-434	No	Rack	IEC 60297-3-103	84HP	11kg	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE