

EuropacPRO Advanced EMC Plus, 19" Subrack Kit for Backplane, Heavy, EMC Shielded, w/wo Front Handle

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.

NEW PRODUCT



VLASTNOSTI

Advanced EMC subrack with on average 60% improved RF shielding effectiveness compared to a standard EuropacPRO, tested according to EN 61000-5-7

Dual mesh top and bottom covers with EMC and airflow optimized perforation, fulfills the requirements of the fire safety standard EN 62368-1

Additional side panel covers for increased lateral RF shielding

Horizontal rails and side panels of type H ("Heavy") for harsh environments

Rear horizontal rail for direct backplane mounting without insulation strip

Shock and vibration resistant up to 5 g, tested in accordance with EN 61373 class 1, category B

Installation load up to 15 kg

Compatible with textile and stainless-steel U-front panel gaskets

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Versions with and without front handles

Supplied as space-saving flat-pack, modifications and assembly services on request

SPECIFIKACE

Static Load:	15kg
Product Type:	Subrack/Chassis
EMC Shielding:	Yes

Table 1/3

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Shock and Vibration Tolerance
24563-920	3U	235mm	1	Backplane	160mm	5g (force)
24563-921	3U	295mm	1	Backplane	160mm	5g (force)
24563-922	3U	295mm	1	Backplane	220mm	5g (force)
24563-923	3U	355mm	1	Backplane	160mm	5g (force)
24563-924	3U	355mm	1	Backplane	220mm	5g (force)
24563-925	3U	355mm	1	Backplane	280mm	5g (force)
24563-930	6U	235mm	1	Backplane	160mm	5g (force)
24563-931	6U	295mm	1	Backplane	160mm	5g (force)
24563-932	6U	295mm	1	Backplane	220mm	5g (force)
24563-933	6U	355mm	1	Backplane	160mm	5g (force)
24563-934	6U	355mm	1	Backplane	220mm	5g (force)
24563-935	6U	355mm	1	Backplane	280mm	5g (force)
24563-970	3U	235mm	1	Backplane	160mm	5g (force)
24563-971	3U	295mm	1	Backplane	160mm	5g (force)
24563-972	3U	295mm	1	Backplane	220mm	5g (force)
24563-973	3U	355mm	1	Backplane	160mm	5g (force)
24563-974	3U	355mm	1	Backplane	220mm	5g (force)

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Shock and Vibration Tolerance
24563-975	3U	355mm	1	Backplane	280mm	5g (force)
24563-980	6U	235mm	1	Backplane	160mm	5g (force)
24563-981	6U	295mm	1	Backplane	160mm	5g (force)
24563-982	6U	295mm	1	Backplane	220mm	5g (force)
24563-983	6U	355mm	1	Backplane	160mm	5g (force)
24563-984	6U	355mm	1	Backplane	220mm	5g (force)
24563-985	6U	355mm	1	Backplane	280mm	5g (force)

Table 2/3						
Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	Povrchová úprava	Materiál	Rack Width
24563-920	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-921	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-922	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-923	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-924	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-925	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-930	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-931	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-932	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP

Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	Povrchová úprava	Materiál	Rack Width
24563-933	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-934	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-935	Yes	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-970	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-971	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-972	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-973	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-974	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-975	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-980	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-981	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-982	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-983	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-984	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP
24563-985	No	Rack	IEC 60297-3-103	Anodized, Passivated	Hliník	84HP

Table 3/3

Katalogové číslo	Gasket Type	Rychlé odeslání
24563-920	Textile EMC, Stainless Steel EMC	Ne
24563-921	Textile EMC, Stainless Steel EMC	Ne

Katalogové číslo	Gasket Type	Rychlé odeslání
24563-922	Textile EMC, Stainless Steel EMC	Ne
24563-923	Textile EMC, Stainless Steel EMC	Ne
24563-924	Textile EMC, Stainless Steel EMC	Ne
24563-925	Textile EMC, Stainless Steel EMC	Ne
24563-930	Textile EMC, Stainless Steel EMC	Ne
24563-931	Textile EMC, Stainless Steel EMC	Ne
24563-932	Textile EMC, Stainless Steel EMC	Ne
24563-933	Textile EMC, Stainless Steel EMC	Ne
24563-934	Textile EMC, Stainless Steel EMC	Ne
24563-935	Textile EMC, Stainless Steel EMC	Ne
24563-970	Textile EMC, Stainless Steel EMC	Ne
24563-971	Textile EMC, Stainless Steel EMC	Ne
24563-972	Textile EMC, Stainless Steel EMC	Ne
24563-973	Textile EMC, Stainless Steel EMC	Ne
24563-974	Textile EMC, Stainless Steel EMC	Ne
24563-975	Textile EMC, Stainless Steel EMC	Ne
24563-980	Textile EMC, Stainless Steel EMC	Ne
24563-981	Textile EMC, Stainless Steel EMC	Ne

Katalogové číslo	Gasket Type	Rychlé odeslání
24563-982	Textile EMC, Stainless Steel EMC	Ne
24563-983	Textile EMC, Stainless Steel EMC	Ne
24563-984	Textile EMC, Stainless Steel EMC	Ne
24563-985	Textile EMC, Stainless Steel EMC	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE