

Front Panel With AC Input Module

Front Panel for CompactPCI Systems with mounted Wide Range AC Input Module containing AC Plug, Fuse Holder and EMC Filter.



CERTIFICATIONS



VLASTNOSTI

Voltage 110 VAC ... 250 VAC, 50 Hz ... 60 Hz

Front panel for shielding with EMC textile gasket

Max. current 10 A at 40°C

SPECIFIKACE

Accessory Type: Front panel

Table 1/2

Katalogové číslo	Materiál	Front Finish	Rear Finish	Rack Height	Výška	Rack Width
------------------	----------	--------------	-------------	-------------	-------	------------

24579-058	Hliník	Anodized	Conductive	3U	128.4mm	8HP
24579-059	Hliník	Anodized	Anodized	3U	261.75mm	8HP

Table 2/2

Katalogové číslo	Šířka	Hloubka	Množství v balení	Povrchová úprava	Rychlé odeslání
24579-058	40.3mm	2.5mm	1	Anodized	Ne
24579-059	40.3mm	2.5mm	1	Anodized	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

EMC profile seals are required to shield the front panels.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE