

Intelligent PDU, EN5xxx, 230 VAC, 1-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



VLASTNOSTI

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFIKACE

Table 1/6

Katalogové číslo	Produktová řada	Typ	Product Type	Typ zásuvky	Socket Quantity	Barva
EN5403	Enlogic	Intelligent PDU	Socket Strip	(30) C13, (6) C19	36	Black
EN5325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN5329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black
EN5337	Enlogic	Intelligent PDU	Socket Strip	(38) C13, (6) C19	44	Black

Table 2/6

Katalogové číslo	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Current Rating	Power Rating	Input Cable Location
------------------	-----------------	------------------	--------------------------	----------------	--------------	----------------------

EN5403	16 A, 1-pole, Hy-Mag	No	0			Top Feed
EN5325	16 A, 1-pole, Hy-Mag	No	2		7.4 kVA	Top Feed
EN5329	16 A, 1-pole, Hy-Mag	No	2		7.4 kVA	Top Feed
EN5337	16 A, 1-pole, Hy-Mag	No	2	32A		Top Feed

Table 3/6

Katalogové číslo	Input Voltage	Phase	Interrupt Rating	Max Power Input	Nominální napětí	On/Off Switch Included
EN5403	400V	3 PH WYE	5kAIC	11.0 kVA		
EN5325	200 – 240V	1 PH	5kAIC	7.44 kVA	230V	No
EN5329	200 – 240V	1 PH	5kAIC	7.44 kVA	230V	No
EN5337	200 – 240V	1 PH	5kAIC	7.44 kVA		

Table 4/6

Katalogové číslo	Output Voltage	Amperage (Derated Amperage)	Plug Type	Rack Units	Removable Input Cable	Metering Type
EN5403	200 – 240VAC	32 A	IEC 60309 516P6 (IP44)	0U	No	Outlet
EN5325	230VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet
EN5329	230VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet
EN5337	200 – 240VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet

Table 5/6

Katalogové číslo	Materiál	Povrchová úprava	Výška	Šířka	Hloubka	Hmotnost
EN5403						
EN5325	Ocel	Strukturovaný Práškový	1780mm	52mm	53mm	8.82kg

Katalogové číslo	Materiál	Povrchová úprava	Výška	Šířka	Hloubka	Hmotnost
EN5329	Ocel	Strukturovaný Práškový	1780mm	52mm	53mm	8.52kg
EN5337						

Table 6/6			
Katalogové číslo	Množství v balení	Input Cable Length	Rychlé odeslání
EN5403	1		Ne
EN5325	1	3m	Ne
EN5329	1	3m	Ne
EN5337	1		Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE