

Intelligent PDU, EN5xxx, 400 VAC, 3-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



VLASTNOSTI

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

SPECIFIKACE

Table 1/6

Katalogové číslo	Produktová řada	Typ	Product Type	Typ zásuvky	Socket Quantity	Barva
EN5402	Enlogic	Intelligent PDU	Socket Strip	(18) C13, (6) C19	24	Black
EN5808	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (12) C19	24	Black
EN5810	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (12) C19	36	Black
EN5812	Enlogic	Intelligent PDU	Socket Strip	(36) C13, (12) C19	48	Black
EN5850	Enlogic	Intelligent PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black

Table 2/6

Katalogové číslo	Switched Outlets	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Input Cable Location	Input Voltage
EN5402	No	No Circuit Breaker	11.0 kVA	0	Top Feed	380 – 415V
EN5808	No	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5810	No	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5812	No	16 A, 1-pole, Hy-Mag		6	Top Feed	400V
EN5850	No	20 A, 1-pole, Hy-Mag	17.3 kVA North America, 22.1 kVA International	6	Top Feed	380 – 415V

Table 3/6

Katalogové číslo	Phase	Interrupt Rating	Nominální napětí	Max Power Input	On/Off Switch Included	Amperage (Derated Amperage)
EN5402	3 PH		415V	11.0 kVA	No	16 A
EN5808	3 PH		415V	22.0 kVA	No	32 A
EN5810	3 PH		415V	22.0 kVA	No	32 A
EN5812	3 PH WYE	5kAIC		22.0 kVA		32 A
EN5850	3 PH		415V	17.3 / 22.1 kVA	No	30 A (24 A) North America, 32 A International

Table 4/6

Katalogové číslo	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Materiál
EN5402	230VAC	0U	IEC 60309 516P6 (IP44)	Outlet	No	Ocel
EN5808	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	Yes	Ocel
EN5810	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	No	Ocel

Katalogové číslo	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Materiál
EN5812	200 – 240VAC	0U	IEC 60309 532P6 (IP44)	Outlet	No	
EN5850	208 – 230VAC	0U	IEC 60309 530P6/532P6	Outlet	No	Ocel

Table 5/6

Katalogové číslo	Povrchová úprava	Výška	Šířka	Hloubka	Hmotnost	Množství v balení
EN5402	Strukturovaný Práškový	1780mm	52mm	53mm	7.82kg	1
EN5808	Strukturovaný Práškový	1780mm	52mm	53mm		1
EN5810	Strukturovaný Práškový	1780mm	85mm	53mm	12.23kg	1
EN5812						1
EN5850	Strukturovaný Práškový	1780mm	56mm	75mm	11.93kg	1

Table 6/6

Katalogové číslo	Input Cable Length	Rychlé odeslání
EN5402	3m	Ne
EN5808	3m	Ne
EN5810	3m	Ne
EN5812		Ne
EN5850	1.8m	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE