

Monitor, Keyboard, Touchpad, 1 U Drawer, Reduced Depth



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



VLASTNOSTI

Pull-out 17" TFT color monitor chassis, 1 U (resolution Full HD; connects to VGA or DVI-D interface)

Keyboard with different keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 450 ... 640 mm

With DVI connection

SPECIFIKACE

Hloubka: 400mm
Product Type: Cabinet/Rack Drawer

Table 1/2

Katalogové číslo	Rack Height	Barva	Kód barvy	Typ	Works With	Keyboard Type
------------------	-------------	-------	-----------	-----	------------	---------------

60118-583	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	QWERTY UK
60118-585	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	AZERTY
60118-584	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	QWERTZ

Table 2/2

Katalogové číslo	Rychlé odeslání
60118-583	Ne
60118-585	Ne
60118-584	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Further versions on request – With trackball or numeric pad.

Other Keyboard layouts see user manual.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE