

Plug-In Unit Kit With Trapezoid Handle, Shielded, Grey



Plug-in unit, with static handle and U-shaped front panel. The grey handle is assembled on the front panel. The U-shaped panel enables the assembly of a textile gasket.

CERTIFICATIONS



VLASTNOSTI

Front panel, U-profile, shielded

Handle without extraction function

SPECIFIKACE

Materiál:	Hliník
Povrchová úprava:	Anodized; Passivated
Product Type:	Front Panel
Typ:	Front Panel with Handle (PIU)
EMC Shielding:	Yes

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Typ rukojeti	Mounting	Gasket Type
20848-663	3U	3HP	1	Trapezoid, Static	Screw-on Front	Textile EMC

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Typ rukojeti	Mounting	Gasket Type
20848-664	3U	4HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-665	3U	5HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-666	3U	6HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-667	3U	7HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-668	3U	8HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-669	3U	10HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-671	6U	3HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-670	3U	12HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-672	6U	4HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-675	6U	7HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-673	6U	5HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-674	6U	6HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-676	6U	8HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-677	6U	10HP	1	Trapezoid, Static	Screw-on Front	Textile EMC
20848-678	6U	12HP	1	Trapezoid, Static	Screw-on Front	Textile EMC

Table 2/3

Katalogové číslo	Front Finish	Rear Finish	Treated Edges	Flammability Rating	Complies With	Výška (H)
20848-663	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm

Katalogové číslo	Front Finish	Rear Finish	Treated Edges	Flammability Rating	Complies With	Výška (H)
20848-664	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-665	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-666	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-667	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-668	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-669	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-671	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-670	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	128.4mm
20848-672	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-675	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-673	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm

Katalogové číslo	Front Finish	Rear Finish	Treated Edges	Flammability Rating	Complies With	Výška (H)
20848-674	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-676	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-677	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm
20848-678	Anodized	Etched	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	261.8mm

Table 3/3

Katalogové číslo	Šířka (W)	Rychlé odeslání
20848-663	14.9mm	Ne
20848-664	20mm	Ne
20848-665	25mm	Ne
20848-666	30.1mm	Ne
20848-667	35.2mm	Ne
20848-668	40.3mm	Ne
20848-669	50.5mm	Ne
20848-671	14.9mm	Ne
20848-670	60.6mm	Ne
20848-672	20mm	Ne

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE