

Plug-In Unit Kit With Trapezoid Handle, Unshielded, Grey



Plug-in unit, with static handle and the flat front panel. The grey handle is assembled on the front panel.

CERTIFICATIONS



VLASTNOSTI

Flat front panel

Handle without extraction function

SPECIFIKACE

Materiál:	Hliník
Povrchová úprava:	Anodized; Passivated
Product Type:	Front Panel
Typ:	Front Panel with Handle (PIU)

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Typ rukojeti	Mounting	Front Finish
20818-017	3U	3HP	1	Trapezoid, Static	Screw-on Front	Anodized

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Typ rukojeti	Mounting	Front Finish
20818-018	3U	4HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-019	3U	5HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-021	3U	7HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-022	3U	8HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-023	3U	10HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-026	6U	5HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-024	3U	12HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-027	6U	6HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-162	6U	7HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-029	6U	10HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-120	6U	12HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-020	3U	6HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-025	6U	4HP	1	Trapezoid, Static	Screw-on Front	Anodized
20818-028	6U	8HP	1	Trapezoid, Static	Screw-on Front	Anodized

Table 2/3

Katalogové číslo	Rear Finish	Treated Edges	Flammability Rating	Complies With	EMC Shielding	Výška (H)
20818-017	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm

Katalogové číslo	Rear Finish	Treated Edges	Flammability Rating	Complies With	EMC Shielding	Výška (H)
20818-018	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm
20818-019	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm
20818-021	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm
20818-022	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm
20818-023	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm
20818-026	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	261.8mm
20818-024	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm
20818-027	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	261.8mm
20818-162	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	261.8mm
20818-029	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	261.8mm
20818-120	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	261.8mm

Katalogové číslo	Rear Finish	Treated Edges	Flammability Rating	Complies With	EMC Shielding	Výška (H)
20818-020	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	128.4mm
20818-025	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	261.8mm
20818-028	Passivated	No	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	No	261.8mm

Table 3/3

Katalogové číslo	Šířka (W)	Rychlé odeslání
20818-017	14.9mm	Ne
20818-018	20mm	Ne
20818-019	25mm	Ne
20818-021	35.2mm	Ne
20818-022	40.3mm	Ne
20818-023	50.5mm	Ne
20818-026	25mm	Ne
20818-024	60.6mm	Ne
20818-027	30.1mm	Ne
20818-162	35.2mm	Ne
20818-029	50.5mm	Ne
20818-120	60.6mm	Ne

