

# PMC Mezzanine Front Panel, Non-Shielded



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments.

## CERTIFICATIONS



## VLASTNOSTI

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

## SPECIFIKACE

Table 1/3

| Katalogové číslo | Typ                        | Accessory Type | Mounting       | EMC Shielding      | Gasket Type | Materiál |
|------------------|----------------------------|----------------|----------------|--------------------|-------------|----------|
| 20835-899        | Mezzanine Front Panel      | Front panel    | Snapped in     | No (Retrofittable) | O-Ring EMC  | Hliník   |
| 20835-896        | Front Panel without Handle |                | Screw-on Front | No (Retrofittable) |             | Zinc     |
| 20835-931        | Front Panel without Handle |                | Screw-on Front | No (Retrofittable) |             | Zinc     |
| 20835-929        | Front Panel without Handle |                | Screw-on Front | No (Retrofittable) |             | Zinc     |

Table 2/3

| Katalogové číslo | Front Finish  | Rear Finish   | Treated Edges | Výška | Šířka  | Complies With             |
|------------------|---------------|---------------|---------------|-------|--------|---------------------------|
| 20835-899        | Anodized      | Conductive    | Yes           | 74mm  | 12.7mm | PMC Mezzanine, IEEE P1386 |
| 20835-896        | Anodized      | Anodized      | No            | 74mm  | 12.7mm | PMC Mezzanine, IEEE P1386 |
| 20835-931        | Anodized      | Conductive    | No            | 74mm  | 12.7mm | PMC Mezzanine, IEEE P1386 |
| 20835-929        | Chrome Plated | Chrome Plated | Yes           | 74mm  | 12.7mm | PMC Mezzanine, IEEE P1386 |

Table 3/3

| Katalogové číslo | Hloubka | Množství v balení | Povrchová úprava | Rychlé odeslání |
|------------------|---------|-------------------|------------------|-----------------|
| 20835-899        | 2.5mm   | 10                | Anodized         | Ne              |
| 20835-896        |         | 10                |                  | Ne              |
| 20835-931        |         | 10                |                  | Ne              |
| 20835-929        |         | 10                |                  | Ne              |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**