

PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

CERTIFICATIONS



VLASTNOSTI

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

SPECIFIKACE

Product Type: Front Panel
Typ: Front Panel without Handle
EMC Shielding: Yes

Table 1/3

Katalogové číslo	Množství v balení	Accessory Type	Mounting	Gasket Type	Front Finish	Rear Finish
20835-598	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-890	1		Screw-on Front			

Katalogové číslo	Množství v balení	AccessoryType	Mounting	Gasket Type	Front Finish	Rear Finish
20835-923	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-922	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-889	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-924	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-893	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-928	10		Screw-on Front		Anodized	Conductive

Table 2/3

Katalogové číslo	Treated Edges	Complies With	Hloubka	Povrchová úprava	Výška	Materiál
20835-598	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Hliník
20835-890	No	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-923	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-922	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-889	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Hliník
20835-924	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-893	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-928	No	PMC Mezzanine, IEEE P1386			74mm	Zinc

Table 3/3

Katalogové číslo	Šířka	Rychlé odeslání
20835-598	12.7mm	Ne
20835-890	12.7mm	Ne
20835-923	12.7mm	Ne
20835-922	12.7mm	Ne
20835-889	12.7mm	Ne
20835-924	12.7mm	Ne
20835-893	12.7mm	Ne
20835-928	12.7mm	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE