


PropacPRO Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



VLASTNOSTI

Desktop case for individual assembly

Ventilation slots in base plate

Retrofitable EMC shielding

Prepared for GND/earthing

Conforms with DIN EN 62368-1

SPECIFIKACE

Product Type:	Case
Typ:	Case for Individual Electronic Components
Produktová řada:	PropacPRO

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
14576-021	2U	42HP	266mm	1	85.1mm	219mm

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
14576-023	2U	42HP	326mm	1	85.1mm	219mm
14576-041	2U	63HP	266mm	1	85.1mm	326mm
14576-043	2U	63HP	326mm	1	85.1mm	326mm
14576-045	2U	63HP	386mm	1	85.1mm	326mm
14576-101	3U	28HP	266mm	1	130mm	148mm
14576-103	3U	28HP	326mm	1	130mm	148mm
14576-121	3U	42HP	266mm	1	130mm	219mm
14576-123	3U	42HP	326mm	1	130mm	219mm
14576-125	3U	42HP	386mm	1	130mm	219mm
14576-141	3U	63HP	266mm	1	130mm	326mm
14576-143	3U	63HP	326mm	1	130mm	326mm
14576-145	3U	63HP	386mm	1	130mm	326mm
14576-161	3U	84HP	266mm	1	130mm	432mm
14576-163	3U	84HP	326mm	1	130mm	432mm
14576-165	3U	84HP	386mm	1	130mm	432mm
14576-167	3U	84HP	446mm	1	130mm	432mm
14576-169	3U	84HP	506mm	1	130mm	432mm
14576-221	4U	42HP	266mm	1	174mm	219mm

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
14576-223	4U	42HP	326mm	1	174mm	219mm
14576-241	4U	63HP	266mm	1	174mm	326mm
14576-243	4U	63HP	326mm	1	174mm	326mm
14576-245	4U	63HP	386mm	1	174mm	326mm
14576-247	4U	63HP	446mm	1	174mm	326mm
14576-265	4U	84HP	386mm	1	174mm	432mm
14576-267	4U	84HP	446mm	1	174mm	432mm
14576-269	4U	84HP	506mm	1	174mm	432mm
14576-463	6U	84HP	326mm	1	262.8mm	432mm
14576-465	6U	84HP	386mm	1	262.8mm	432mm
14576-467	6U	84HP	446mm	1	262.8mm	432mm
14576-469	6U	84HP	506mm	1	262.8mm	432mm

Table 2/3

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
14576-021	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	111mm
14576-023	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	111mm
14576-041	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	111mm

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
14576-043	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	111mm
14576-045	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	111mm
14576-101	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-103	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-121	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-123	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-125	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-141	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-143	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-145	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-161	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-163	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-165	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-167	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
14576-169	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14576-221	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-223	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-241	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-243	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-245	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-247	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-265	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-267	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-269	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14576-463	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	289mm
14576-465	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	289mm
14576-467	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	289mm
14576-469	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	289mm

Table 3/3

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Šířka	Rychlé odeslání
14576-021	Hliník	IP20	25kg	257mm	Ne
14576-023	Hliník	IP20	25kg	257mm	Ne
14576-041	Hliník	IP20	25kg	363.7mm	Ne
14576-043	Hliník	IP20	25kg	363.7mm	Ne
14576-045	Hliník	IP20	25kg	363.7mm	Ne
14576-101	Hliník	IP20	25kg	185.9mm	Ne
14576-103	Hliník	IP20	25kg	185.9mm	Ne
14576-121	Hliník	IP20	25kg	257mm	Ne
14576-123	Hliník	IP20	25kg	257mm	Ne
14576-125	Hliník	IP20	25kg	257mm	Ne
14576-141	Hliník	IP20	25kg	363.7mm	Ne
14576-143	Hliník	IP20	25kg	363.7mm	Ne
14576-145	Hliník	IP20	25kg	363.7mm	Ne
14576-161	Hliník	IP20	25kg	470.3mm	Ne
14576-163	Hliník	IP20	25kg	470.3mm	Ne
14576-165	Hliník	IP20	25kg	470.3mm	Ne
14576-167	Hliník	IP20	25kg	470.3mm	Ne
14576-169	Hliník	IP20	25kg	470.3mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Šířka	Rychlé odeslání
14576-221	Hliník	IP20	25kg	257mm	Ne
14576-223	Hliník	IP20	25kg	257mm	Ne
14576-241	Hliník	IP20	25kg	363.7mm	Ne
14576-243	Hliník	IP20	25kg	363.7mm	Ne
14576-245	Hliník	IP20	25kg	363.7mm	Ne
14576-247	Hliník	IP20	25kg	363.7mm	Ne
14576-265	Hliník	IP20	25kg	470.3mm	Ne
14576-267	Hliník	IP20	25kg	470.3mm	Ne
14576-269	Hliník	IP20	25kg	470.3mm	Ne
14576-463	Hliník	IP20	25kg	470.3mm	Ne
14576-465	Hliník	IP20	25kg	470.3mm	Ne
14576-467	Hliník	IP20	25kg	470.3mm	Ne
14576-469	Hliník	IP20	25kg	470.3mm	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Case, 2 U with side panel for tip-up carrying handle on request.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE