


PropacPRO Portable Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition this case is prepared for the fitting of a tip-up carrying handle, which is part of the extensive accessory range.

CERTIFICATIONS



VLASTNOSTI

Desktop case for individual assembly

Prepared with holes for fitting of tip-up carrying handle

Retrofitable EMC shielding

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

Prepared for GND/earthing

Conforms with DIN EN 62368-1

SPECIFIKACE

Product Type:	Case
Typ:	Case for Individual Electronic Components
Produktová řada:	PropacPRO

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
------------------	-------------	------------	---------	-------------------	---------------	--------------

14577-123	3U	42HP	326mm	1	130mm	219mm
14577-125	3U	42HP	386mm	1	130mm	219mm
14577-143	3U	63HP	326mm	1	130mm	326mm
14577-145	3U	63HP	386mm	1	130mm	326mm
14577-163	3U	84HP	326mm	1	130mm	432mm
14577-165	3U	84HP	386mm	1	130mm	432mm
14577-223	4U	42HP	326mm	1	174mm	219mm
14577-243	4U	63HP	326mm	1	174mm	326mm
14577-245	4U	63HP	386mm	1	174mm	326mm
14577-265	4U	84HP	386mm	1	174mm	432mm

Table 2/3

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
14577-123	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14577-125	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14577-143	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14577-145	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14577-163	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm
14577-165	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	155.5mm

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
14577-223	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14577-243	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14577-245	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm
14577-265	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Strukturovaný Práškový	200mm

Table 3/3

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Šířka	Rychlé odeslání
14577-123	Hliník	IP20	25kg	257mm	Ne
14577-125	Hliník	IP20	25kg	257mm	Ne
14577-143	Hliník	IP20	25kg	363.7mm	Ne
14577-145	Hliník	IP20	25kg	363.7mm	Ne
14577-163	Hliník	IP20	25kg	470.3mm	Ne
14577-165	Hliník	IP20	25kg	470.3mm	Ne
14577-223	Hliník	IP20	25kg	257mm	Ne
14577-243	Hliník	IP20	25kg	363.7mm	Ne
14577-245	Hliník	IP20	25kg	363.7mm	Ne
14577-265	Hliník	IP20	25kg	470.3mm	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order tip up carrying handle separatly.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE