

PSU 19" AC/DC Linear Regulator, Dual

Linear regulator for application which only allows a very low noise level at the outputs.



CERTIFICATIONS



VLASTNOSTI

2 output voltages, galvanically separated

High control accuracy, low residual ripple and very low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

SPECIFIKACE

Table 1/3

Katalogové číslo	Typ	Vstupní napětí AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-017	19" Linear Regulator	230V	10W	2	12V	0.4A
13105-018	19" Linear Regulator	230V	12W	2	15V	0.4A
13105-022	19" Linear Regulator	230V	24W	2	12V	1A

Katalogové číslo	Typ	Vstupní napětí AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-023	19" Linear Regulator	230V	30W	2	15V	1A
13105-021	19" Linear Regulator	230V	14W	2	5V	1.4A
13105-027	19" Linear Regulator	230V	36W	2	12V	1.5A
13105-028	19" Linear Regulator	230V	45W	2	15V	1.5A
13105-029	19" Linear Regulator	230V	58W	2	24V	1.2A

Table 2/3

Katalogové číslo	Voltage 2	Current 2	Rack Height	Rack Width	Hloubka	Množství v balení
13105-017	12V	0.4A	3U	6HP	171.93mm	1
13105-018	15V	0.4A	3U	6HP	171.93mm	1
13105-022	12V	1A	3U	10HP	171.93mm	1
13105-023	15V	1A	3U	10HP	171.93mm	1
13105-021	5V	1.4A	3U	10HP	171.93mm	1
13105-027	12V	1.5A	3U	14HP	171.93mm	1
13105-028	15V	1.5A	3U	14HP	171.93mm	1
13105-029	24V	1.2A	3U	14HP	171.93mm	1

Table 3/3

Katalogové číslo	Certifications	Rychlé odeslání
13105-017	RoHS, CE, EN 62368-1	Ne
13105-018	CE, EN 62368-1, RoHS	Ne

Katalogové číslo	Certifications	Rychlé odeslání
13105-022	CE, RoHS	Ne
13105-023	RoHS, CE	Ne
13105-021	RoHS, CE	Ne
13105-027	CE, RoHS	Ne
13105-028	RoHS, CE	Ne
13105-029	CE, RoHS	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE