

PSU 19" AC/DC Linear Regulator, Single

Linear regulator for applications requiring very low output noise level.



CERTIFICATIONS



VLASTNOSTI

1 output voltage

High control accuracy, low residual ripple and low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

SPECIFIKACE

Table 1/2

Katalogové číslo	Typ	Vstupní napětí AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-004	19" Linear Regulator	230V	16W	1	24V	0.6A
13105-003	19" Linear Regulator	230V	15W	1	15V	1A
13105-002	19" Linear Regulator	230V	13W	1	12V	1.1A

Katalogové číslo	Typ	Vstupní napětí AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-001	19" Linear Regulator	230V	8W	1	5V	1.5A
13105-006	19" Linear Regulator	230V	20W	1	5V	4A
13105-013	19" Linear Regulator	230V	53W	1	15V	3.5A
13105-014	19" Linear Regulator	230V	60W	1	24V	2.5A
13105-012	19" Linear Regulator	230V	50W	1	12V	4.2A
13105-007	19" Linear Regulator	230V	31W	1	12V	2.8A
13105-011	19" Linear Regulator	230V	30W	1	5V	6A
13105-008	19" Linear Regulator	230V	33W	1	15V	2.2A
13105-009	19" Linear Regulator	230V	36W	1	24V	1.5A

Table 2/2

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Certifications	Rychlé odeslání
13105-004	3U	6HP	171.93mm	1	RoHS, CE, EN 62368-1	Ne
13105-003	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS	Ne
13105-002	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS	Ne
13105-001	3U	6HP	171.93mm	1	EN 62368-1, CE, RoHS	Ne
13105-006	3U	10HP	171.93mm	1	CE, RoHS	Ne
13105-013	3U	14HP	171.93mm	1	RoHS, CE	Ne
13105-014	3U	14HP	171.93mm	1	RoHS, CE	Ne

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Certifications	Rychléodeslání
13105-012	3U	14HP	171.93mm	1	CE, RoHS	Ne
13105-007	3U	10HP	171.93mm	1	CE, RoHS	Ne
13105-011	3U	14HP	171.93mm	1	CE, RoHS	Ne
13105-008	3U	10HP	171.93mm	1	CE, RoHS	Ne
13105-009	3U	10HP	171.93mm	1	CE, RoHS	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE