

PSU 19" AC/DC Maxpower 180 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

CERTIFICATIONS



VLASTNOSTI

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active Power Factor Correction (PFC)

1 output voltage

Signalling: Output voltage OK

Efficiency up to 87 %

Integrated active decoupling for redundancy operation

Active Current Share Bus (CSB)

SPECIFIKACE

Table 1/2

Katalogové číslo	Typ	Vstupní napětí AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-153	19" Switched-Mode	90 – 264V	168W	1	24V	7A
13100-151	19" Switched-Mode	90 – 264V	156W	1	12V	13A

Katalogové číslo	Typ	Vstupní napětí AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-152	19" Switched-Mode	90 – 264V	165W	1	15V	11A
13100-150	19" Switched-Mode	90 – 264V	150W	1	5V	30A

Table 2/2

Katalogové číslo	Rack Height	Rack Width	Množství v balení	Rychlé odeslání
13100-153	3U	8HP	1	Ne
13100-151	3U	8HP	1	Ne
13100-152	3U	8HP	1	Ne
13100-150	3U	8HP	1	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please order front panel separately.

Output data for mains voltage > 190 VAC, TA = 0 ... 50 °C.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE