

Rack Safety Plus, 3 U, 208 / 240 V AC



VLASTNOSTI

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

208 V phase to phase or phase to neutral or 240 V phase to phase mains input

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

UL pending

SPECIFIKACE

Function:	Emergency Stop
Inrush Current Limiter:	No
Residual Current Device:	No
Circuit Breaker Cover:	No
Works With:	Varistar CP; Novastar
Accessory Type:	Power distribution accessories

Table 1/2

Katalogové číslo	Product Type	Vstupní napětí AC	Počet fází	EMC Filter	Surge Arrester	Rack Height
21272-001	Power Distributor	208 – 240V	1	Yes	Yes	3U
21272-003	Power Distributor	208 – 240V	1	No	No	3U

Table 2/2

Katalogové číslo	Typ zásuvky	Množství v balení	Rychlé odeslání
21272-001	IEC C13, IEC C19	1	Ne
21272-003	IEC C13 lockable	1	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE