


RatiopacPRO 19" Case, Retrofittable Shielding With Handles



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides front handles for easier handling of the case.

CERTIFICATIONS



VLASTNOSTI

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Version with front handles

Retrofittable EMC shielding

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

Symmetrical design, identical front and rear side

No visible screws; cladding parts removable without tools

Conforms with DIN EN 62368-1

SPECIFIKACE

Product Type:	Case
Produktová řada:	RatiopacPRO

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
24571-838	6U	84HP	375.5mm	1	245.7mm	432mm
24571-839	6U	84HP	435.5mm	1	245.7mm	432mm
24571-840	6U	84HP	495.5mm	1	245.7mm	432mm
24572-213	5U	28HP	255.5mm	1	201.25mm	148mm
24572-216	5U	28HP	315.5mm	1	201.25mm	148mm
24572-225	5U	42HP	255.5mm	1	201.25mm	219mm
24572-228	5U	42HP	315.5mm	1	201.25mm	219mm
24572-229	5U	42HP	375.5mm	1	201.25mm	219mm
24572-237	5U	63HP	255.5mm	1	201.25mm	326mm
24572-240	5U	63HP	315.5mm	1	201.25mm	326mm
24572-241	5U	63HP	375.5mm	1	201.25mm	326mm
24572-249	5U	84HP	255.5mm	1	201.25mm	432mm
24572-252	5U	84HP	315.5mm	1	201.25mm	432mm
24572-253	5U	84HP	375.5mm	1	201.25mm	432mm
24572-254	5U	84HP	435.5mm	1	201.25mm	432mm
24572-255	5U	84HP	495.5mm	1	201.25mm	432mm
24572-357	5U	28HP	255.5mm	1	201.25mm	148mm
24572-360	5U	28HP	315.5mm	1	201.25mm	148mm

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
24572-369	5U	42HP	255.5mm	1	201.25mm	219mm
24572-372	5U	42HP	315.5mm	1	201.25mm	219mm
24572-373	5U	42HP	375.5mm	1	201.25mm	219mm
24572-381	5U	63HP	255.5mm	1	201.25mm	326mm
24572-384	5U	63HP	315.5mm	1	201.25mm	326mm
24572-385	5U	63HP	375.5mm	1	201.25mm	326mm
24572-393	5U	84HP	255.5mm	1	201.25mm	432mm
24572-396	5U	84HP	315.5mm	1	201.25mm	432mm
24572-397	5U	84HP	375.5mm	1	201.25mm	432mm
24572-398	5U	84HP	435.5mm	1	201.25mm	432mm
24572-399	5U	84HP	495.5mm	1	201.25mm	432mm
24572-720	2U	42HP	248.74mm	1	88.1mm	213.94mm
24572-723	2U	42HP	248.74mm	1	88.1mm	213.94mm
24572-730	2U	63HP	355.42mm	1	88.1mm	320.62mm
24572-733	2U	63HP	35.42mm	1	88.1mm	32.62mm
24571-702	3U	28HP	255.5mm	1	112.3mm	148mm
24571-705	3U	28HP	315.5mm	1	112.3mm	148mm
24571-714	3U	42HP	255.5mm	1	112.3mm	219mm

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
24571-717	3U	42HP	315.5mm	1	112.3mm	219mm
24571-718	3U	42HP	375.5mm	1	112.3mm	219mm
24571-726	3U	63HP	255.5mm	1	112.3mm	326mm
24571-729	3U	63HP	315.5mm	1	112.3mm	326mm
24571-730	3U	63HP	375.5mm	1	112.3mm	326mm
24571-738	3U	84HP	255.5mm	1	112.3mm	432mm
24571-741	3U	84HP	315.5mm	1	112.3mm	432mm
24571-742	3U	84HP	375.5mm	1	112.3mm	432mm
24571-743	3U	84HP	435.5mm	1	112.3mm	432mm
24571-744	3U	84HP	495.5mm	1	112.3mm	432mm
24571-750	4U	28HP	255.5mm	1	156.8mm	148mm
24571-753	4U	28HP	315.5mm	1	156.8mm	148mm
24571-762	4U	42HP	255.5mm	1	156.8mm	219mm
24571-765	4U	42HP	315.5mm	1	156.8mm	219mm
24571-766	4U	42HP	375.5mm	1	156.8mm	219mm
24571-774	4U	63HP	255.5mm	1	156.8mm	326mm
24571-777	4U	63HP	315.5mm	1	156.8mm	326mm
24571-778	4U	63HP	375.5mm	1	156.8mm	326mm

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
24571-786	4U	84HP	255.5mm	1	156.8mm	432mm
24571-789	4U	84HP	315.5mm	1	156.8mm	432mm
24571-790	4U	84HP	375.5mm	1	156.8mm	432mm
24571-791	4U	84HP	435.5mm	1	156.8mm	432mm
24571-792	4U	84HP	495.5mm	1	156.8mm	432mm
24571-798	6U	28HP	255.5mm	1	245.7mm	148mm
24571-801	6U	28HP	315.5mm	1	245.7mm	148mm
24571-810	6U	42HP	255.5mm	1	245.7mm	219mm
24571-813	6U	42HP	315.5mm	1	245.7mm	219mm
24571-814	6U	42HP	375.5mm	1	245.7mm	219mm
24571-822	6U	63HP	255.5mm	1	245.7mm	326mm
24571-825	6U	63HP	315.5mm	1	245.7mm	326mm
24571-826	6U	63HP	375.5mm	1	245.7mm	326mm
24571-834	6U	84HP	255.5mm	1	245.7mm	432mm
24571-837	6U	84HP	315.5mm	1	245.7mm	432mm

Table 2/3

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
------------------	--------------------------	----------------	---------------	---------------	------------------	-------

24571-838	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-839	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-840	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24572-213	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-216	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-225	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-228	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-229	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm

24572-237	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-240	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-241	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-249	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-252	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-253	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-254	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-255	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm

24572-357	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-360	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-369	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-372	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-373	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-381	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-384	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-385	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm

24572-393	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-396	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-397	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-398	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-399	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	221.5mm
24572-720	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Strukturovaný Práškový	88.1mm
24572-723	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Strukturovaný Práškový	88.1mm
24572-730	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Strukturovaný Práškový	88.1mm

24572-733	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Yes	Passivated, Strukturovaný Práškový	88.1mm
24571-702	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-705	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-714	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-717	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-718	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-726	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-729	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm

24571-730	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-738	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-741	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-742	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-743	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-744	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	132.6mm
24571-750	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-753	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm

24571-762	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-765	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-766	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-774	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-777	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-778	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-786	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-789	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm

24571-790	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-791	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-792	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	177mm
24571-798	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-801	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-810	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-813	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-814	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm

24571-822	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-825	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-826	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-834	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm
24571-837	Handles, Horizontal Rails	No	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Passivated, Strukturovaný Práškový	265.9mm

Table 3/3

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Typ	Šířka	Rychlé odeslání
24571-838	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-839	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-840	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Typ	Šířka	Rychléodeslání
24572-213	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24572-216	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24572-225	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24572-228	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24572-229	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24572-237	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24572-240	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24572-241	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24572-249	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-252	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-253	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Typ	Šířka	Rychléodeslání
24572-254	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-255	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-357	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24572-360	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24572-369	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24572-372	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24572-373	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24572-381	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24572-384	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24572-385	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24572-393	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Typ	Šířka	Rychléodeslání
24572-396	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-397	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-398	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-399	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24572-720	Hliník	IP20		Case for 19" Components	235.5mm	Ne
24572-723	Hliník	IP20		Case for 19" Components	235.5mm	Ne
24572-730	Hliník	IP20		Case for 19" Components	342.4mm	Ne
24572-733	Hliník	IP20		Case for 19" Components	342.4mm	Ne
24571-702	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24571-705	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24571-714	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-717	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Typ	Šířka	Rychléodeslání
24571-718	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-726	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-729	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-730	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-738	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-741	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-742	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-743	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-744	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-750	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24571-753	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Typ	Šířka	Rychléodeslání
24571-762	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-765	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-766	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-774	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-777	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-778	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-786	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-789	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-790	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-791	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-792	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Typ	Šířka	Rychléodeslání
24571-798	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24571-801	Hliník	IP20	25kg	Case for Individual Electronic Components	164.4mm	Ne
24571-810	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-813	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-814	Hliník	IP20	25kg	Case for Individual Electronic Components	235.5mm	Ne
24571-822	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-825	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-826	Hliník	IP20	25kg	Case for Individual Electronic Components	342.4mm	Ne
24571-834	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne
24571-837	Hliník	IP20	25kg	Case for Individual Electronic Components	448.9mm	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE