


RatiopacPRO Style, Front Handles and Rear Circulating Trim, Screwless Front



The versatile RatiopacPRO Style desktop case features a protective frame design, rubber strips, and various configuration options.

The Front and Rear Trims with Top & Bottom Rubber Strip option provides connector safeguarding and integrated stacking capability. The Circulated Rubber Strip design protects corner and is ideal for smaller mobile cases. For larger equipment, the Front Handle offers convenient carrying and rear connector protection.

Designed for 19" components with guide rails or proprietary components with a mounting plate, RatiopacPRO Style caters to your specific requirements.

VLASTNOSTI

Desktop case with protective frame design and front handles for a easy handling. Rear side with a circulating rubber strip to protect the enclosure during the transport

Case for 19" components (guide rails) or proprietary components (mounting plate)

To establish EMC-shielding, additional components need to be added to the enclosure

Front side for front panel mounting without screws and rear side prepared for standard front panel mounting

Perforated bottom cover for air-cooling

No visible screws; cladding parts removable without tools

For board depth 160 mm, 220 mm, 280 mm and 340 mm (depending on case depth)

SPECIFIKACE

Product Type:	Case
Typ:	Case for Individual Electronic Components
Produktová řada:	RatiopacPRO Style

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
24580-314	3U	28HP	322mm	1	112.3mm	142.8mm

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
24580-315	3U	28HP	382mm	1	112.3mm	142.8mm
24580-324	3U	42HP	322mm	1	112.3mm	213.9mm
24580-325	3U	42HP	382mm	1	112.3mm	213.9mm
24580-326	3U	42HP	442mm	1	112.3mm	213.9mm
24580-334	3U	63HP	322mm	1	112.3mm	320.6mm
24580-335	3U	63HP	382mm	1	112.3mm	320.6mm
24580-336	3U	63HP	442mm	1	112.3mm	320.6mm
24580-344	3U	84HP	322mm	1	112.3mm	427.3mm
24580-345	3U	84HP	382mm	1	112.3mm	427.3mm
24580-346	3U	84HP	442mm	1	112.3mm	427.3mm
24580-347	3U	84HP	502mm	1	112.3mm	427.3mm
24580-424	4U	42HP	322mm	1	156.8mm	213.9mm
24580-425	4U	42HP	382mm	1	156.8mm	213.9mm
24580-426	4U	42HP	442mm	1	156.8mm	213.9mm
24580-434	4U	63HP	322mm	1	156.8mm	320.6mm
24580-435	4U	63HP	382mm	1	156.8mm	320.6mm
24580-436	4U	63HP	442mm	1	156.8mm	320.6mm
24580-444	4U	84HP	322mm	1	156.8mm	427.3mm

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Usable Height	Usable Width
24580-445	4U	84HP	382mm	1	156.8mm	427.3mm
24580-446	4U	84HP	442mm	1	156.8mm	427.3mm
24580-447	4U	84HP	502mm	1	156.8mm	427.3mm

Table 2/3						
Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
24580-314	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-315	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-324	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-325	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-326	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
24580-334	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-335	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-336	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-344	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-345	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-346	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm
24580-347	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	157mm

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
24580-424	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-425	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-426	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-434	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-435	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-436	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-444	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm

Katalogové číslo	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Povrchová úprava	Výška
24580-445	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-446	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm
24580-447	Side Trim, Horizontal Rails	Yes	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	Anodized, Passivated, Strukturovaný Práškový	201mm

Table 3/3

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Šířka	Rychlé odeslání
24580-314	Hliník	IP30	25kg	176.4mm	Ne
24580-315	Hliník	IP30	25kg	176.4mm	Ne
24580-324	Hliník	IP30	25kg	247.5mm	Ne
24580-325	Hliník	IP30	25kg	247.5mm	Ne
24580-326	Hliník	IP30	25kg	247.5mm	Ne
24580-334	Hliník	IP30	25kg	354.2mm	Ne
24580-335	Hliník	IP30	25kg	354.2mm	Ne
24580-336	Hliník	IP30	25kg	354.2mm	Ne
24580-344	Hliník	IP30	25kg	460.9mm	Ne
24580-345	Hliník	IP30	25kg	460.9mm	Ne

Katalogové číslo	Materiál	Stupeň krytí	Static Load	Šířka	Rychlé odeslání
24580-346	Hliník	IP30	25kg	460.9mm	Ne
24580-347	Hliník	IP30	25kg	460.9mm	Ne
24580-424	Hliník	IP30	25kg	247.5mm	Ne
24580-425	Hliník	IP30	25kg	247.5mm	Ne
24580-426	Hliník	IP30	25kg	247.5mm	Ne
24580-434	Hliník	IP30	25kg	354.2mm	Ne
24580-435	Hliník	IP30	25kg	354.2mm	Ne
24580-436	Hliník	IP30	25kg	354.2mm	Ne
24580-444	Hliník	IP30	25kg	460.9mm	Ne
24580-445	Hliník	IP30	25kg	460.9mm	Ne
24580-446	Hliník	IP30	25kg	460.9mm	Ne
24580-447	Hliník	IP30	25kg	460.9mm	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

For custom configurations (colors, sizes, etc.), please visit our online configurator (<https://configurators.schroff.biz/ratiopacpro-style>).

Modification service for customer specific versions on request (special colours, sizes, cut-outs, etc.).

Assembly service from lotsize 1.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE