

Varistar CP EMC Cabinet, IP 55



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

VLASTNOSTI

Shielding 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3)

Shielding 30 dB at 18 GHz, (tested to EN 61000-5-7) with EN45545 gaskets

Type of protection IP 55

Static load-carrying capacity 1600 kg

Doors with 4-point locking and screw-fixed side panels

Side and rear panels can be installed by one person

SPECIFIKACE

Static Load:	1600kg
Product Type:	Cabinet
Stupeň krytí:	IP55
Cladding Color Code:	RAL 7021
Frame Material:	Ocel

Table 1/3

Katalogové číslo	Rack Height	Výška	Frame Color	Šířka	Frame Color Code	Vstup kabelu
10630-044	42U	2000mm	Black Grey	600mm	RAL 7021	Yes
10630-043	42U	2000mm	Black Grey	600mm	RAL 7021	No

Table 2/3

Katalogové číslo	Cladding Material	Hloubka	Cladding Color	Množství v balení	Complies With	Povrchová úprava
10630-044	Ocel	800mm	Black Grey	1	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Strukturovaný Práškový
10630-043	Ocel	800mm	Black Grey	1	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Strukturovaný Práškový

Table 3/3

Katalogové číslo	Materiál	Rychlé odeslání
10630-044	Ocel	Ne
10630-043	Ocel	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrti a/nebo zničit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE