

Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking



EMC and IP55 Steel Door with lever handle and 4-Point locking.

VLASTNOSTI

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

SPECIFIKACE

Product Type: Cabinet Door

Stupeň krytí: IP55

Materiál: Ocel

Table 1/2

Katalogové číslo	Rack Height	Výška	Šířka	Množství v balení	Complies With	Povrchová úprava
21630-760	33U	1600mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový
21630-761	33U	1600mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový

Katalogové číslo	Rack Height	Výška	Šířka	Množství v balení	Complies With	Povrchová úprava
21630-762	38U	1800mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový
21630-763	38U	1800mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový
21630-764	42U	2000mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový
21630-765	42U	2000mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový
21630-766	47U	2200mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový
21630-767	47U	2200mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Strukturovaný Práškový

Table 2/2

Katalogové číslo	Locking Type	Typ	Works With	Rychlé odeslání
21630-760	4-Point Locking	Steel Door, Plain	Varistar CP	Ne
21630-761	4-Point Locking	Steel Door, Plain	Varistar CP	Ne
21630-762	4-Point Locking	Steel Door, Plain	Varistar CP	Ne
21630-763	4-Point Locking	Steel Door, Plain	Varistar CP	Ne
21630-764	4-Point Locking	Steel Door, Plain	Varistar CP	Ne
21630-765	4-Point Locking	Steel Door, Plain	Varistar CP	Ne
21630-766	5-Point Locking	Steel Door, Plain	Varistar CP	Ne

Katalogové číslo	Locking Type	Typ	Works With	Rychlé odeslání
21630-767	5-Point Locking	Steel Door, Plain	Varistar CP	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE