

Varistar CP Server Cabinet



Welded steel frame for high static load requirements.
Prepared for 19" integration of IT assets.

VLASTNOSTI

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFIKACE

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Ocel

Table 1/2

Katalogové číslo	Rack Height	Výška	Cladding Material	Šířka	Cladding Color	Hloubka
10630-018	42U	2000mm	Ocel	800mm	Black Grey	1200mm

Katalogové číslo	Rack Height	Výška	Cladding Material	Šířka	Cladding Color	Hloubka
10630-020	47U	2200mm	Ocel	800mm	Black Grey	1200mm
10630-017	42U	2000mm	Ocel	600mm	Black Grey	1200mm
10630-019	47U	2200mm	Ocel	600mm	Black Grey	1200mm
10630-023	42U	2000mm	Ocel	600mm	Black Grey	1200mm
10630-024	42U	2000mm	Ocel	800mm	Black Grey	1200mm
10630-025	47U	2200mm	Ocel	600mm	Black Grey	1200mm
10630-026	47U	2200mm	Ocel	800mm	Black Grey	1200mm

Table 2/2

Katalogové číslo	Typ	Množství v balení	Dynamic Load	Povrchová úprava	Materiál	Rychlé odeslání
10630-018	Standard	1	1000kgf	Strukturovaný Práškový	Ocel	Ne
10630-020	Standard	1	1000kgf	Strukturovaný Práškový	Ocel	Ne
10630-017	Standard	1	1000kgf	Strukturovaný Práškový	Ocel	Ne
10630-019	Standard	1	1000kgf	Strukturovaný Práškový	Ocel	Ne
10630-023	Side-by-Side	1	1000kgf	Strukturovaný Práškový	Ocel	Ne
10630-024	Side-by-Side	1	1000kgf	Strukturovaný Práškový	Ocel	Ne
10630-025	Side-by-Side	1	1000kgf	Strukturovaný Práškový	Ocel	Ne
10630-026	Side-by-Side	1	1000kgf	Strukturovaný Práškový	Ocel	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná

instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE