

Varistar CP Steel Door, Perforated With 1-Point Locking



Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

VLASTNOSTI

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

SPECIFIKACE

Product Type: Cabinet Door

Stupeň krytí: IP20

Materiál: Ocel

Table 1/2

Katalogové číslo	Rack Height	Výška	Šířka	Locking Type	Množství v balení	Barva
21630-507	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-408	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-508	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-409	24U	1200mm	800mm	Single Point Locking	1	Black Grey

Katalogové číslo	Rack Height	Výška	Šířka	Locking Type	Množství v balení	Barva
21630-509	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-410	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-510	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-411	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-511	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-412	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-512	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-413	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-513	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-414	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-514	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-415	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-515	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-006	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-516	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-013	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-517	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-007	47U	2200mm	600mm	Single Point Locking	1	Black Grey

Katalogové číslo	Rack Height	Výška	Šířka	Locking Type	Množství v balení	Barva
21630-518	47U	2200mm	800mm	Single Point Locking	1	Black Grey
21630-014	47U	2200mm	800mm	Single Point Locking	1	Black Grey
21630-008	52U	2450mm	600mm	Single Point Locking	1	Black Grey
21630-015	52U	2450mm	800mm	Single Point Locking	1	Black Grey

Table 2/2

Katalogové číslo	Kód barvy	Complies With	Typ	Works With	Rychlé odeslání
21630-507	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-408	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-508	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-409	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-509	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-410	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-510	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-411	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-511	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-412	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-512	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-413	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-513	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne

Katalogové číslo	Kód barvy	Complies With	Typ	Works With	Rychlé odeslání
21630-414	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-514	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-415	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-515	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-006	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-516	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-013	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-517	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-007	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-518	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP	Ne
21630-014	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-008	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne
21630-015	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP	Ne

DALŠÍ PODROBNOSTI O PRODUKTU

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit

selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE