

BC200-CD Conduit to Beam Clamp



CERTIFICERINGER



FUNKTIONER

Eliminates offset bending conduit

Threaded hole on back

Ideal for electrical, mechanical, and HVAC applications

SPECIFIKATIONER


Table 1/2

Katalognummer	Artikelnummer	Materiale	Finish	Outer Diameter (OD)	Flange Thickness (FT)	Rod Size (RS)
BC200CD1B	182220	Stål	Electrogalvanized	19 - 25 mm	16 mm Max	6

Table 2/2

Katalognummer	Artikelnummer	Torque (TQ)	Static Load
BC200CD1B	182220	4 N·m	440N

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

