

nVent CADDY Pyramid Tool-Free Pipe Clamp



FUNKTIONER

Push-in clamps install without the need for additional tools or strut clamps

Clamps come in two different sizes to fit project needs

Plastic clamps and base will not corrode pipe

SPECIFIKATIONER

Materiale: Nylon
Temperature: -45 to 65 °C

Table 1/1

Katalognummer	Artikelnummer	Outer Diameter (OD)	Length (L)	Width (W)	A	Unit Weight
PTF1C	360484	12.7 - 22.4 mm	40.6mm	19.1 mm	9.5 mm	0.01 kg
PTF2C	360485	21.3 - 60.3 mm	81.3mm	19.1 mm	9.5 mm	0.02 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

