

nVent CADDY Speed Link SLK Spool Kit



FUNKTIONER

Kit includes spool of nVent CADDY Speed Link steel wire and nVent CADDY Speed Link SLK locking devices

Wire spool and locking devices are packaged together, simplifying transportation to the jobsite and reducing inventory

Packaging allows end-users to pull and cut any length of wire that is needed without having to take the spool out of the box

Ideal for rework and installations where custom lengths of wire may be needed

Wire rope constructed from seven bundles of seven strands each of steel aircraft wire

Push/pull keyless release allows easy adjustments

Low-profile locking device minimizes visual impact

Cable spread of 90 degrees allows positioning the device closer to the load

Keyless release tubes are easy to operate while wearing gloves

Double-sided locking mechanism enables simple height adjustment

SPECIFIKATIONER

Finish: Electrogalvanized

Materiale: Stål

Table 1/1

Katalognummer	Artikelnummer	Wire Rope Diameter	Length	Number of Locking Devices
SLK15L500PACK	196045	1.5 mm	150m	100

Katalognummer	Artikelnummer	Wire Rope Diameter	Length	Number of Locking Devices
SLK15L50MPACK	196046	1.5 mm	50m	25
SLK2L100PACK	196047	2 mm	100m	50

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

