

PEMSA Wire Basket Tray Quick Base Joint



CERTIFICERINGER



FUNKTIONER

Quick and easy to use

Eliminates the need for additional hardware

Suitable for 300 to 600mm wide tray, and heights of 60 and 100mm

IEC 61537 load rating and earthing compliant

SPECIFIKATIONER

Finish: Electrogalvanized

Materiale: Stål

Table 1/2

Katalognummer	Artikelnummer	Farve	Diameter	Hole Size 1	Hole Size 2	Length
WBTQBCLIPBG	820708	Black	4.0 - 4.5 mm	9 mm	7.5 mm	91.5mm
WBTQBCLIPBG	820713		4.0 - 4.5 mm	9 mm	7.5 mm	91.5mm

Table 2/2

Katalognummer	Artikelnummer	Width	Height	Certificeringer
WBTQBCLIPBG	820708	59 mm	14.5 mm	CE, CADDY WBTQBCLIPBG, UKCA, CADDY WBTQBCLIPBG, CE, CADDY EU WBT QB2
WBTQBCLIPBG	820713	59 mm	14.5 mm	CE, CADDY WBTQBCLIPBG, UKCA, CADDY WBTQBCLIPBG

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

