

SOSR Stand Off Two Hole Strap for CPVC Pipe



CERTIFICERINGER



FUNKTIONER

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Positions pipe 1-1/2" (38 mm) off the mounting surface eliminating the need for wooden spacer blocks

Can be mounted in both vertical and horizontal positions on concrete, steel and wood

Meets the UL® 203 stringent upward thrust requirement

UL® Listed as both a hanger and pipe restraint

Complies with static load requirements of NFPA® 13

Includes mounting screws

Can be used with 3TW backing nut on composite wood joist installations

SPECIFIKATIONER

Finish: Pregalvanized

Materiale: Stål


Table 1/2

Katalognummer	Artikelnummer	NB/DN	Hole Size (HS)	A	B	C
SOSR200	597809	50	5.1 mm	102 mm	133 mm	25.4 mm
SOSR150	597808	40	5.1 mm	98 mm	114 mm	25.4 mm
SOSR100	597806	25	5.1 mm	75 mm	94 mm	25.4 mm
SOSR125	597807	32	5.1 mm	84 mm	92 mm	25.4 mm
SOSR075	597805	20	5.1 mm	68 mm	92 mm	25.4 mm

Table 2/2

Katalognummer	Artikelnummer	Thickness (T)	Hanger Spacing
SOSR200	597809	1.61 mm	2.4 m Max
SOSR150	597808	1.61 mm	2.1 m Max
SOSR100	597806	1.3 mm	1.8 m Max
SOSR125	597807	1.61 mm	1.95 m Max
SOSR075	597805	1.3 mm	1.65 m Max

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl,

materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

