

19" Drawer

Data Solutions



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICERINGER



FUNKTIONER

Static load-carrying capacity 15 kg

Optional writing surface

SPECIFIKATIONER

Static Load: 15kg
Product Type: Cabinet/Rack Drawer
Materiale: Stål

Table 1/2

Katalognummer	Rack Height	Finish	Pakke mængde	Farve	Farvekode	Front Finish
20110-054	1U	Struktur Pulvermaling	1	Light Grey	RAL 7035	

Katalognummer	Rack Height	Finish	Pakke mængde	Farve	Farvekode	Front Finish
20110-061	1U	Struktur Pulvermaling	1			Anodized
20110-180	1U	Struktur Pulvermaling	1	Black Grey	RAL 7021	
20110-055	2U	Struktur Pulvermaling	1	Light Grey	RAL 7035	
20110-056	3U	Struktur Pulvermaling	1	Light Grey	RAL 7035	
20110-062	2U	Struktur Pulvermaling	1			Anodized
20110-063	3U	Struktur Pulvermaling	1			Anodized
20110-181	2U	Struktur Pulvermaling	1	Black Grey	RAL 7021	
20110-182	3U	Struktur Pulvermaling	1	Black Grey	RAL 7021	

Table 2/2

Katalognummer	Type	Works With
20110-054	Drawer	19" Cabinets
20110-061	Drawer	19" Cabinets
20110-180	Drawer	19" Cabinets
20110-055	Drawer	19" Cabinets
20110-056	Drawer	19" Cabinets
20110-062	Drawer	19" Cabinets
20110-063	Drawer	19" Cabinets
20110-181	Drawer	19" Cabinets
20110-182	Drawer	19" Cabinets

YDERLIGERE PRODUKTOPLYSNINGER

Please order 19" assembly kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE