

Cable to Web of Rail Mold Only, Power

Data Solutions



FUNKTIONER

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

Connections for power or grounding conductor to the neutral axis

SPECIFIKATIONER

Materiale: Graphite

Bond Terminal Style: W

Table 1/1

Katalognummer	Artikelnummer	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBWX2LH		85 lb to 141 lb T-Rail Sections	35 mm ² Concentric	7.75mm	T20	Left Hand
PBWX2RH		85 lb to 141 lb T-Rail Sections	35 mm ² Concentric	7.75mm	T20	Right Hand
PBWX3RH	227045	85 lb to 141 lb T-Rail Sections	50 mm ² Ropelay	9.27mm	T20	Right Hand
PBW2CLH		85 lb to 141 lb T-Rail Sections	1/0 Concentric	9.5mm	T20	Left Hand

Katalognummer	Artikelnummer	Rail Type	Conductor Size	Conductor OuterDiameter, Nominal	Welder Style	Orientation
PBW2CRH		85 lb to 141 lb T-Rail Sections	1/0 Concentric	9.5mm	T20	Right Hand
PBW2GLH		85 lb to 141 lb T-Rail Sections	2/0 Concentric	10.62mm	T20	Left Hand
PBW2GRH		85 lb to 141 lb T-Rail Sections	2/0 Concentric	10.62mm	T20	Right Hand
PBW2JLH		85 lb to 141 lb T-Rail Sections	2/0 Ropelay	12.19mm	T20	Left Hand
PBW2JRH		85 lb to 141 lb T-Rail Sections	2/0 Ropelay	12.19mm	T20	Right Hand
PBW2QLH		85 lb to 141 lb T-Rail Sections	4/0 Concentric	13.41mm	T20	Left Hand
PBW2QRH		85 lb to 141 lb T-Rail Sections	4/0 Concentric	13.41mm	T20	Right Hand
PBWS6LH		85 lb to 141 lb T-Rail Sections	3/0 Composite	14.53mm	T20	Left Hand
PBWS6RH		85 lb to 141 lb T-Rail Sections	3/0 Composite	14.53mm	T20	Right Hand
PBW2SLH		85 lb to 141 lb T-Rail Sections	4/0 Ropelay	15.49mm	T20	Left Hand
PBW2SRH		85 lb to 141 lb T-Rail Sections	4/0 Ropelay	15.49mm	T20	Right Hand
PBWX5LH		85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	15.52mm	T20	Left Hand
PBWX5RH		85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	15.52mm	T20	Right Hand
PBWX7LH		85 lb to 141 lb T-Rail Sections	150 mm ² Ropelay	17.04mm	T20	Left Hand
PBWX7RH		85 lb to 141 lb T-Rail Sections	150 mm ² Ropelay	17.04mm	T20	Right Hand
PBW2W010LH		R13, RI52	250 kcmil Ropelay	19.05mm	T20	Left Hand
PBW2W010RH		R13, RI52	250 kcmil Ropelay	19.05mm	T20	Right Hand
PBW2WLH		85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	T20	Left Hand

Katalognummer	Artikelnummer	Rail Type	Conductor Size	Conductor OuterDiameter, Nominal	Welder Style	Orientation
PBW2WLK1LH		LK1 Girder Rail	250 kcmil Ropelay	19.05mm	T20	Left Hand
PBW2WLK1RH		LK1 Girder Rail	250 kcmil Ropelay	19.05mm	T20	Right Hand
PBW2WRH		85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	T20	Right Hand
PBWX8LH		85 lb to 141 lb T-Rail Sections	185 mm ² Ropelay	20.19mm	T20	Left Hand
PBWX8RH		85 lb to 141 lb T-Rail Sections	185 mm ² Ropelay	20.19mm	T20	Right Hand
PBW3FRH		85 lb to 141 lb T-Rail Sections	350 kcmil Ropelay	22.35mm	T20	Right Hand
PBWX902LH		85 lb to 141 lb T-Rail Sections	240 mm ² Ropelay	23.62mm	T20	Left Hand
PBWX902RH		85 lb to 141 lb T-Rail Sections	240 mm ² Ropelay	23.62mm	T20	Right Hand
PBW3S002LH		RI60	500 kcmil Ropelay	26.42mm	T20	Left Hand
PBW3S002RH		RI60	500 kcmil Ropelay	26.42mm	T20	Right Hand
PBW3SLH		85 lb to 141 lb T-Rail Sections	500 kcmil Ropelay	26.42mm	T20	Left Hand
PBW3SLK1LH		LK1 Girder Rail	500 kcmil Ropelay	26.42mm	T20	Left Hand
PBW3SLK1RH		LK1 Girder Rail	500 kcmil Ropelay	26.42mm	T20	Right Hand
PBW3SRH		85 lb to 141 lb T-Rail Sections	500 kcmil Ropelay	26.42mm	T20	Right Hand

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE