

Cable to Web of Rail T20 Complete Welder Pair, Power

Data Solutions



FUNKTIONER

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Each part number Includes both right and left hand welders

Includes mold cleaner and flint ignitor

SPECIFIKATIONER

Materiale: Graphite; Stål; Thermoplastic

Bond Terminal Style: W

Table 1/1

Katalognummer	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBWT20Y301	UIC	50 mm ² Concentric	8.9mm	T20
PBWT20X3	UIC	50 mm ² Ropelay	9.13mm	T20
PBWT202C	85 lb to 141 lb T-Rail Sections	1/0 Concentric	9.47mm	T20

Katalognummer	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBWT202G	85 lb to 141 lb T-Rail Sections	2/0 Concentric	10.62mm	T20
PBWT202E	85 lb to 141 lb T-Rail Sections	1/0 Ropelay	10.87mm	T20
PBWT20X401	85 lb to 141 lb T-Rail Sections	70 mm ² Ropelay	10.92mm	T20
PBWT202J	85 lb to 141 lb T-Rail Sections	2/0 Ropelay	12.19mm	T20
PBWT202Q	85 lb to 141 lb T-Rail Sections	4/0 Concentric	13.41mm	T20
PBWT20S6	85 lb to 141 lb T-Rail Sections	14.5 mm Diameter	14.5mm	T20
PBWT202S	85 lb to 141 lb T-Rail Sections	4/0 Ropelay	15.49mm	T20
PBWT20X5	UIC	95 mm ² Ropelay	15.52mm	T20
PBXLWT20X5	85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	15.52mm	T20
PBWT20X7	UIC	150 mm ² Ropelay	17.04mm	T20
PBWT203D	85 lb to 141 lb T-Rail Sections	350 kcmil Concentric	17.3mm	T20
PBWT20X8	85 lb to 141 lb T-Rail Sections	185 mm ² Ropelay	17.8mm	T20
PBWT202W	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	T20
PBWT202W135	135 lb Bethlehem	250 kcmil Ropelay	19.05mm	T20
PBWT202W20AS	20 lb ASCE	250 kcmil Ropelay	19.05mm	T20
PBWT20W40AS	40 lb ASCE	250 kcmil Ropelay	19.1mm	T20
PBWT203B	85 lb to 141 lb T-Rail Sections	300 kcmil Ropelay	20.32mm	T20
PBWT203F	85 lb to 141 lb T-Rail Sections	350 kcmil Ropelay	22.35mm	T20

Katalognummer	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBWT20X901	85 lb to 141 lb T-Rail Sections	240 mm ² Ropelay	23.62mm	T20
PBWT203S	85 lb to 141 lb T-Rail Sections	500 kcmil Ropelay	26.42mm	T20

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE