


DIN Rail

Data Solutions

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



FUNKTIONER

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

SPECIFIKATIONER

Product Type: DIN Rail

Table 1/2

Katalognummer	Materiale	Højde	Length	Finish	Pakke mængde	Dybde
20118-872	Stål	35mm	125mm	Forzinket Stål	4	15mm
20118-873	Stål	35mm	175mm	Forzinket Stål	4	15mm
20118-874	Stål	35mm	275mm	Forzinket Stål	4	15mm
20118-875	Stål	35mm	375mm	Forzinket Stål	4	15mm
20118-876	Stål	35mm	475mm	Forzinket Stål	4	15mm

Katalognummer	Materiale	Højde	Length	Finish	Pakke mængde	Dybde
20118-877	Stål	35mm	575mm	Forzinket Stål	4	15mm
20118-878	Stål	35mm	125mm	Forzinket Stål	4	7.5mm
20118-879	Stål	35mm	175mm	Forzinket Stål	4	7.5mm
20118-880	Stål	35mm	275mm	Forzinket Stål	4	7.5mm
20118-881	Stål	35mm	375mm	Forzinket Stål	4	7.5mm
20118-882	Stål	35mm	475mm	Forzinket Stål	4	7.5mm
20118-883	Stål	35mm	575mm	Forzinket Stål	4	7.5mm
20118-890	Stål	35mm	125mm	Forzinket Stål	10	7.5mm
20118-891	Stål	35mm	175mm	Forzinket Stål	10	7.5mm
20118-892	Stål	35mm	275mm	Forzinket Stål	10	7.5mm
20118-893	Stål	35mm	375mm	Forzinket Stål	10	7.5mm
20118-894	Stål	35mm	475mm	Forzinket Stål	10	7.5mm
20118-895	Stål	35mm	575mm	Forzinket Stål	10	7.5mm
20118-884	Stål	35mm	125mm	Forzinket Stål	10	15mm
20118-885	Stål	35mm	175mm	Forzinket Stål	10	15mm
20118-886	Stål	35mm	275mm	Forzinket Stål	10	15mm
20118-887	Stål	35mm	375mm	Forzinket Stål	10	15mm
20118-888	Stål	35mm	475mm	Forzinket Stål	10	15mm

Katalognummer	Materiale	Højde	Length	Finish	Pakke mængde	Dybde
20118-889	Stål	35mm	575mm	Forzinket Stål	10	15mm

Table 2/2

Katalognummer	Bredde
20118-872	125mm
20118-873	175mm
20118-874	275mm
20118-875	375mm
20118-876	475mm
20118-877	575mm
20118-878	125mm
20118-879	175mm
20118-880	275mm
20118-881	375mm
20118-882	475mm
20118-883	575mm
20118-890	125mm
20118-891	175mm
20118-892	275mm
20118-893	375mm

Katalognummer	Bredde
20118-894	475mm
20118-895	575mm
20118-884	125mm
20118-885	175mm
20118-886	275mm
20118-887	375mm
20118-888	475mm
20118-889	575mm

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE