


Joint Bond T8 Complete Welder Pair, Power, 50 mm² Ropelay

Data Solutions

KATALOGNUMMER

PBCT8X3



FUNKTIONER

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

Includes mold cleaner and flint ignitor

PRODUKTEGENSKABER

Materiale: Graphite; Stål; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: C

Conductor Size: 50 mm² Ropelay

Conductor Outer Diameter, Nominal: 9.13mm

Bond Length: 177.8mm

Welder Style: T8

Mold Only: No

Replacement Mold: PBCX3

Welding Material: PB45, Sold Separately

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE